

YNA56RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA56RT](#)



HYLUG™, Al Compression Terminal , 1510-1590 kcmil ACSR 1700-1800 kcmil ALUM. 1650 kcmil ACAR 42-19 STR, 4 Pad holes, 13.76 in Length.

Features

- Compression Terminal with 4-hole pad

Application

For use on: ACSR, ACAR and SAC Transmission Lines

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1650 KCMIL (42/19 STR)
Conductor - ACAR Str Size	1650 KCMIL (42/19 STR)
Conductor - AL Str Size	1700 KCMIL -1800 KCMIL
Conductor - AL Str Size Range	1700 KCMIL -1800 KCMIL
Conductor - ACSR Str Size	1510.5 (45/7) Nuthatch kcmil - 1590 (54/19) Falcon kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) Nuthatch kcmil - 1590 (54/19) Falcon kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.44 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	350 mm
Dimension - Outside Diameter inch	2.5 in
Dimension - Width fraction	3.44 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	13.76 in

General

Trade Name	HYLUG™
Die Index	729
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
UPC	781810016411
Type	YNA-RT EHV
Material	Aluminum
UPC 12 Digit	781810016411
UPC 14 Digit GTIN	00781810016411

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)