



# YNA59RT15, ACSR - 15 Degree Compression Terminal

By Burndy  
Catalog # [YNA59RT15](#)



HYLUG™, Compression terminal for ACSR, ACAR and AAC, 2156-2167 Kcmil ACSR, 2250-2300 Kcmil Aluminum, Cable to Flat, 15 Deg

### Features

- ACSR Compression Terminal
- 15 Degree Angle

### Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

### Conductor

|                                 |                                                                                                                |
|---------------------------------|----------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Size         | <ul style="list-style-type: none"><li>• 2250 kcmil</li><li>• 2300 kcmil</li></ul>                              |
| Conductor - AL Str Size Range   | 2250 kcmil-2300 kcmil                                                                                          |
| Conductor - ACSR Str Size       | <ul style="list-style-type: none"><li>• 2156 (84/19) Bluebird kcmil</li><li>• 2167 (72/7) Kiwi kcmil</li></ul> |
| Conductor - ACSR Str Size Range | 2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil                                                             |

### Configuration

|                                      |                 |
|--------------------------------------|-----------------|
| Physical Attribute - Pad Orientation | 15 Degree Angle |
| Connector Type                       | Terminal        |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Pad Width inch      | 3.57 in  |
| Dimension - Bolt Hole Size inch | 0.56 in  |
| Package Height                  | 0.000 in |

|                                              |           |
|----------------------------------------------|-----------|
| Package Weight                               | 0.000 lb. |
| Package Length                               | 0.000 in  |
| Dimension - E Spacing between Holes fraction | 1-3/4 in  |
| Package Width                                | 0.000 in  |
| Dimension - L Length Overall mm              | 349 mm    |
| Dimension - Outside Diameter inch            | 2.5 in    |
| Dimension - Length Side A inch               | 13.75 in  |
| Dimension - Length Side B inch               | 13.54 in  |
| Dimension - Width fraction                   | 3.57 in   |
| Dimension - Length Overall inch              | 13.75 in  |

### General

|                           |                |
|---------------------------|----------------|
| Trade Name                | HYLUG™         |
| Die Index                 | 735            |
| UPC                       | 781810141120   |
| Prefilled Oxide Inhibitor | Y              |
| Material                  | Aluminum       |
| UPC 12 Digit              | 781810141120   |
| UPC 14 Digit GTIN         | 00781810141120 |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 360 |
| Carton Quantity       | 4   |

### Product Assets

[Catalog \[English\]](#)