



YNA59RT15H, Aluminum Terminal, 15° Angle

By Burndy
Catalog # [YNA59RT15H](#)



HYLUG™, Compression terminal for ACSR, ACAR and AAC, 2156-2167 Kcmil ACSR, 2250-2300 Kcmil Aluminum, Cable to Flat, 15 Deg, Terminal available with H/W

Features

- Aluminum Compression Terminal
- 15 Degree Angle
- Supplied with Hardware

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2250 kcmil • 2300 kcmil
Conductor - AL Str Size Range	• 2250 kcmil • 2300 kcmil
Conductor - ACSR Str Size	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil

Configuration

Physical Attribute - Pad Orientation	15 Degree Angle
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.57 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	349 mm
Dimension - Outside Diameter inch	2.5 in
Dimension - Width fraction	3.57 in
Dimension - Length Overall inch	13.75 in

General

Trade Name	HYLUG™
Die Index	735
UPC	781810120446
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810120446
UPC 14 Digit GTIN	00781810120446

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)