

YNA7M6T, Aluminum Terminal, 2-hole

By Burndy
Catalog # [YNA7M6T](#)

Al Compression Static Wire Terminal, 2 Holes, 7#6 Alumoweld,
1/2"(7 Str) EHS Steel, 0.56" Hole Dia.



Features

- Aluminum Compression Terminal
- 2-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Galvanized Steel	1/2 (19) in
Str Size	
Conductor - Galvanized Steel	1/2 (19) in
Str Size Range	
Conductor Type	GAL Steel C Str-Size

Configuration

Physical Attribute - Pad	Straight
Orientation	
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.5 in
Dimension - Bolt Hole Size inch	0.56 in

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall	249 mm
Dimension - B Length inch	4.10 in
Dimension - Outside Diameter inch	1.18 in
Dimension - Length Overall inch	9.8 in

General

Die Index	• 679 • 789
UPC	781810016428
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016428
UPC 14 Digit GTIN	00781810016428

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)