



YNA7M9T, Alumoweld - EHS Steel Compression Terminal

By Burndy
Catalog # [YNA7M9T](#)



Steel Compression terminal for Alumoweld and EHS Steel to
dead end, 7 #9, 3 #6 Alumoweld

Features

- Alumoweld-EHS Steel Compression Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	GAL Steel C Str-Size
----------------	----------------------

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.5 in
Dimension - Bolt Hole Size inch	0.56 in

Dimension - E Spacing between Holes fraction 1-3/4 in

Dimension - L Length Overall mm 223 mm

Dimension - B Length inch 2.79 in

Dimension - Outside Diameter inch 0.8 in

Dimension - Length Overall inch 8.79 in

General

Die Index	677
UPC	781810081549
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810081549
UPC 14 Digit GTIN	00781810081549

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[Catalog \[English\]](#)