



YNM428, 4-outlet HYCRAB Connector

By Burndy
Catalog # [YNM428](#)

HYCRAB 4 OUTLET 4/0 STR



Features

- 4-Outlet HYCRAB Connector

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	
Conductor - Copper Str Size	4/0 AWG

Dimensions

Dimension - Height inch	3.19 in
Dimension - Height fraction	3-3/16 in

Dimension - B Length fraction	2 in
Dimension - Length Overall	8.19 in
inch	

General

Plated	Y
UPC	621945469228
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810101919
UPC 14 Digit GTIN	00781810101919

Logistics

Minimum Pack Quantity	6
Pallet Quantity	864
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)