



YNS32RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS32RT](#)



HYSPLICE™, ACCOM: 300 kcmil - 336.4 KCMIL ACSR, 336.4 kcmil
- 350 kcmil ALUM, 395.1 kcmil - 395.2 kcmil ACAR,INDEX: 717

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	395.1 KCMIL - 395.2 KCMIL
Conductor - ACAR Str Size	• 395.1 • 395.2
Conductor - AL Str Size	336.4 KCMIL - 350 KCMIL
Conductor - AL Str Size Range	336.4 KCMIL - 350 KCMIL
Conductor - ACSR Str Size	• 336.4 (26/7) Linnet • 336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	• 336.4 (26/7) Linnet • 336.4 (30/7) Oriole

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	228 mm
Dimension - Outside Diameter	1.19 in
Dimension - Diameter Max Size	1.19 in
Dimension - Length Overall	8.96 in

General

Trade Name	HYSPLICE™
Die Index	717
UPC	781810515020
Material	Aluminum
UPC 12 Digit	781810515020
UPC 14 Digit GTIN	00781810515020

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)