



YNS34R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS34R](#)



HYSPLICE™, ACCOM: 397.5 kcmil ACSR 397.5 kcmil ALUM - 477 kcmil ALUM INDEX: 719

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	397.5 KCMIL - 477 KCMIL
Conductor - AL Str Size Range	397.5 KCMIL - 477 KCMIL
Conductor - ACSR Str Size	397.5 (26/7) lbis kcmil
Conductor - ACSR Str Size Range	397.5 (26/7) lbis kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	220 mm
mm	
Dimension - Outside Diameter	1.3 in
inch	
Dimension - Length Overall	8.68 in
inch	

General

Trade Name	HYSPLICE™
Die Index	719
UPC	781810515037
Material	Aluminum
UPC 12 Digit	781810515037
UPC 14 Digit GTIN	00781810515037

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2700
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)