



YNS36R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS36R](#)



HYSPLICE™ , AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 500-556.5 Kcmil AL, 477 Kcmil ACSR, 230 kV

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	500 KCMIL - 556.5 KCMIL
Conductor - AL Str Size Range	500 KCMIL - 556.5 KCMIL
Conductor - ACSR Str Size	477 KCMIL
Conductor - ACSR Str Size Range	477 KCMIL

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	234 mm
Dimension - Outside Diameter	1.41 inch
Dimension - Length Overall	9.2 inch

General

Trade Name	HYSPLICE™
Die Index	720
UPC	781810097465
Material	Aluminum
UPC 12 Digit	781810097465
UPC 14 Digit GTIN	00781810097465

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)