



YNS39R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS39R](#)



HYSPLICE™ , AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 634.9-653.1 Kcmil ACAR, 600-650 Kcmil AL, 556.5 Kcmil ACSR, 230 kV

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	556.5 KCMIL
Conductor - AL Str Size	600 kcmil - 650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil
Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	248 mm
Dimension - Outside Diameter	1.50 in
Dimension - Length Overall	9.76 in

General

Trade Name	HYSPLICE™
Die Index	722
UPC	781810085851
Material	Aluminum
UPC 12 Digit	781810085851
UPC 14 Digit GTIN	00781810085851

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)