

YNS43R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS43R](#)



HYSPLICE™ Jumper Loop Sleeve, Al Tube, 605 - 666.6 kcmil
ACSR, 700 - 800 kcmil Al, 230 kV, 9.98" L, 724 Index

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil
Conductor - ACSR Str Size	• 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil • 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	253 mm
mm	
Dimension - Outside Diameter	1.61 in
inch	
Dimension - Length Overall	9.98 in
inch	

General

Trade Name	HYSPLICE™
Die Index	724
UPC	781810016121
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016121
UPC 14 Digit GTIN	00781810016121

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)