



YNS451R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS451R](#)



HYSPLICE™ Al Tube Jumper Loop Sleeve, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(Al), 715.5-874.5 kcmil(ACSR), 10.04" L, For ACSR Cond.

Features

- Compression Jumper Sleeve

Application

For ACSR And Stranded Aluminum Cable Up To And Including 230 KV

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	840.2 kcmil-927.2 kcmil
Conductor - AL Str Size	• 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - AL Str Size Range	750 kcmil-1000 kcmil
Conductor - ACSR Str Size	• 715.5 (54/7) Crow kcmil • 715.5 (24/7) Stilt kcmil • 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil • 795 (30/19) Mallard kcmil • 874.5 (54/7) Crane kcmil

Conductor - ACSR Str Size Range	715.5 (54/7) Crow kcmil-874.5 (54/7) Crane kcmil
---------------------------------	--

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	255 mm
Dimension - Outside Diameter inch	1.80 in
Dimension - Length Overall inch	10.04 in

General

Trade Name	HYSPLICE™
Die Index	725
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
UPC	781810094495
Type	YNS-R
Construction Material - Main Material	Aluminum
UPC 12 Digit	781810094495
UPC 14 Digit GTIN	00781810094495

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)