



YNS451RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS451RT](#)



HYSPLICE™ Al Tube Jumper Loop Sleeve, For EHV, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(Al), 715.5-874.5 kcmil(ACSR), 230 kV, 10.60" L, 725 Index

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	715.5 KCMIL - 874.5 KCMIL
Conductor - AL Str Size	795 KCMIL - 1000 KCMIL
Conductor - AL Str Size Range	795 KCMIL - 1000 KCMIL
Conductor - ACSR Str Size	• 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) Starling kcmil-795 (54/7) Condor kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	269 mm
Dimension - Outside Diameter	1.80 in
Dimension - Diameter Max Size	1.80 in
Dimension - Length Overall	10.60 in

General

Trade Name	HYSPLICE™
Die Index	725
UPC	781810016497
Material	Aluminum
UPC 12 Digit	781810016497
UPC 14 Digit GTIN	00781810016497

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1008
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)