



YNS451RTHT, Aluminum Loop Splice

By Burndy
Catalog # [YNS451RTHT](#)



Aluminum loop Hysplice, 715.5-874.5 kcmil ACSS, 18.60 in long

Features

- Aluminum Compression Loop Splice

Specifications

Standards - RoHS Compliance CM
Status

Conductor

- Conductor - ACSR Str Size
- 715.5 (54/7) Crow
 - 715.5 (26/7) Starling
 - 715.5 (30/19) Redwing
 - 795 (54/7) Condor
 - 795 (26/7) Drake
 - 795 (30/7) Mallard
 - 874.5 (54/7) Crane
- Conductor - AL Str Size
- 715.5
 - 795.5
 - 800
 - 874.5

Configuration

Connector Type Splice

Dimensions

Dimension - Outside Diameter	1.8 in
inch	
Dimension - L Length Overall	472 mm
mm	
Length	18.6 in
Dimension - Length Overall	18.6 in
inch	
Width	1.8 in

General

Die Index	725
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 14 Digit GTIN	00781810480311
Material	Aluminum
Plating Type	Unplated
UPC	781810480311

Logistics

Minimum Pack Quantity	5
Carton Quantity	6
Pallet Quantity	576

Product Assets

[Catalog \[English\]](#)