

YNS49R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS49R](#)



HYSPLICE™ Al Tube Jumper Loop Sleeve, 900 -1113 kcmil(ACAR), 1033.5-1272 kcmil(Al), 900-1113 kcmil 45/7Str(ACSR), 230 kV, 10.08" L

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACAR Str Size	• 950 (37) kcmil • 1000 (61) kcmil • 1100 (61) kcmil • 1200 (61) kcmil
Conductor - AL Str Size	1033.5 KCMIL - 1272 KCMIL
Conductor - AL Str Size Range	1033.5 KCMIL - 1272 KCMIL
Conductor - ACSR Str Size	• 900 (54/7) Canary kcmil • 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil • 1033.5 (54/7) Curlew kcmil • 1113 (54/19) Finch kcmil
Conductor - ACSR Str Size Range	900 (54/7) Canary kcmil-1113 (54/19) Finch kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	256 mm
Dimension - Outside Diameter	1.97 in
Dimension - Length Overall	10.08 in

General

Trade Name	HYSPLICE™
Die Index	727
UPC	781810085875
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810085875
UPC 14 Digit GTIN	00781810085875

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1008
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)