

YNS49RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS49RT](#)



HYSPLICE™ Al Tube Jumper Loop Sleeve, 900 - 1113 Kcmil ACSR,
1033.5 - 1272 Kcmil Al,983.1 - 1198 Kcmil ACAR, above 230 kV

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - AL Str Size	1033.5 KCMIL - 1272 KCMIL
Conductor - AL Str Size Range	1033.5 KCMIL - 1272 KCMIL
Conductor - ACSR Str Size	• 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil • 1033.5 (54/7) Curlew kcmil • 900 (45/7) Ruddy kcmil • 1113 (45/7) Bluejay kcmil
Conductor - ACSR Str Size Range	900 (45/7) Canary kcmil-1113 (45/7) Bluejay kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	271 mm
Dimension - Outside Diameter inch	1.97 in
Dimension - Diameter Max Size inch	1.97 in
Dimension - Length Overall inch	10.66 in

General

Trade Name	HYSPLICE™
Die Index	727
UPC	781810016480
Material	Aluminum
UPC 12 Digit	781810016480
UPC 14 Digit GTIN	00781810016480

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1080
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)