



YNS52RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS52RT](#)



HYSPLICE™, ACCOM: 1113 54-19 STR - 135 kcmil ACSR 1277-1280
kcmil ACSR 1351.5-1510 kcmil AL INDEX: 728 T&B 189

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1277 KCMIL - 1280 KCMIL
Conductor - AL Str Size	1351.5 KCMIL - 1510 KCMIL
Conductor - AL Str Size Range	1351.5 KCMIL - 1510 KCMIL
Conductor - ACSR Str Size	• 1113 (54/19) Finch kcmil • 1192.5 (45/7) Bunting kcmil • 1192.5 (54/19) Grackle kcmil • 1272 (54/19) Pheasant kcmil • 1351.5 (54/19) Martin kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Finch kcmil-1351.5 (54/19) Martin kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	411 mm
Dimension - Outside Diameter	2.25 in
Dimension - Diameter Max Size	2.25 in
Dimension - Length Overall	16.20 in

General

Trade Name	HYSPLICE™
Die Index	728
UPC	781810180631
Material	Aluminum
UPC 12 Digit	781810180631
UPC 14 Digit GTIN	00781810180631

Logistics

Minimum Pack Quantity	1
Pallet Quantity	384
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)