

YNS54R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS54R](#)



HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 1534 Kcmil ACAR, 1590-1600 Kcmil AL, 1431 Kcmil ACSR

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1534 KCMIL
Conductor - AL Str Size	1590 KCMIL - 1600 KCMIL
Conductor - AL Str Size Range	1590 KCMIL - 1600 KCMIL
Conductor - ACSR Str Size	1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1431 (54/19) Plover kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	393 mm
Dimension - Outside Diameter	2.25 in
Dimension - Length Overall	15.48 in

General

Trade Name	HYSPLICE™
Die Index	728
UPC	781810180648
Material	Aluminum
UPC 12 Digit	781810180648
UPC 14 Digit GTIN	00781810180648

Logistics

Minimum Pack Quantity	1
Pallet Quantity	384
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)