



YNS56R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS56R](#)



HYSPLICE™ AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 1650 Kcmil ACAR, 1700-1800 Kcmil AL, 1510.5-1590 Kcmil ACSR

Features

- ACSR Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1650 KCMIL - 42/19 STR
Conductor - ACSR Cmpt Run Range	1510.5 KCMIL - 1590 KCMIL
Conductor - AL Str Size	1700 KCMIL - 1800 KCMIL
Conductor - AL Str Size Range	1700 KCMIL - 1800 KCMIL
Conductor - ACSR Str Size	• 1510.5 (45/7) Nuthatch kcmil • 1590 (45/7) Lapwing kcmil • 1590 (54/19) Falcon kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) Nuthatch kcmil-1590 (54/19) Falcon kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	376 mm
Dimension - Outside Diameter inch	2.50 in
Dimension - Length Overall inch	14.8 in

General

Trade Name	HYSPLICE™
Die Index	729
UPC	781810081624
Material	Aluminum
UPC 12 Digit	781810081624
UPC 14 Digit GTIN	00781810081624

Logistics

Minimum Pack Quantity	1
Pallet Quantity	288
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)



A Hubbell brand