

YNS58RT, Aluminum Splice

By Burndy
Catalog # [YNS58RT](#)



HYSPLICE™, ACCOM: 1780kcmil ACSR 2000kcmil ALUM INDEX:
BURNDY 735 T&B 212,214

Features

- Aluminum Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2000 KCMIL
Conductor - AL Str Size Range	2000 KCMIL
Conductor - ACSR Str Size	1780 (84/19) Chukar kcmil
Conductor - ACSR Str Size Range	1780 (84/19) Chukar kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	393 mm
	mm
Dimension - Outside Diameter	2.50 in
	inch
Dimension - Diameter Max Size	2.50 in
	inch
Dimension - Length Overall	15.46 in
	inch

General

Trade Name	HYSPLICE™
Die Index	735
UPC	781810112748
Material	Aluminum
UPC 12 Digit	781810112748
UPC 14 Digit GTIN	00781810112748

Logistics

Minimum Pack Quantity	1
Pallet Quantity	384
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)