

YNS594R, Aluminum Jumper Loop Sleeve

By Burndy
Catalog # [YNS594R](#)



HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 2267-2500 Kcmil ACAR, 2500 Kcmil AL, 2300 Kcmil ACSR, 230 kV

Features

- Aluminum Jumper Loop Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	2267 KCMIL - 2500 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	357 mm
Dimension - Outside Diameter inch	2.60 in
Dimension - Length Overall inch	14.04 in

General

Trade Name	HYSPLICE™
Die Index	740
UPC	781810469774
Material	Aluminum
UPC 12 Digit	781810469774
UPC 14 Digit GTIN	00781810469774

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)