



YNU32R, Aluminum Repair Sleeve

By Burndy
Catalog # [YNU32R](#)



Al Repair sleeve, HV and EHV applications, 300-336.4 Kcmil ACSR, 14 IN L, 717 Index, For temporary restoration of conductivity to damaged ACSR Trnsmsn. Lines

Features

- Aluminum Repair Sleeve
- High and Extra High Voltage Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size Range	336.4 Kcmil - 350 Kcmil
Conductor - ACSR Str Size Range	300 Kcmil - 336.4 Kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	356 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Length Overall inch	14.00 in

General

Die Index	717
UPC	781810180860
Material	Aluminum
UPC 12 Digit	781810180860
UPC 14 Digit GTIN	00781810180860

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)