

YOT361R361R, Aluminum T-Tap Connector

By Burndy
Catalog # [YOT361R361R](#)

Aluminum T-Tap Connector, 426 or M index, 477 (18-1) ACSR 477 (19, 37) AAC



Features

- Aluminum T-Tap Connector

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Run	30.58 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - ACSR Str Run	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Run Range	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Tap	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Tap Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Run	477 kcmil
Conductor - AL Str Run Range	477 kcmil
Conductor - AL Str Tap	477 kcmil
Conductor - AL Str Tap Range	477 kcmil
Conductor - AAAC 5005 Run	30.58 (7) kcmil
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	314 mm
Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Package Height	0.000 in
Dimension - Height mm	158.8 mm
Length	12.37 in
Dimension - Length Overall inch	12.375 in
Width	1.34 in
Height	6.25 in
Dimensions	12.37 in x 1.34 in x 6.25 in

General

Plated	N
Prefilled Oxide Inhibitor	Y
UPC 14 Digit GTIN	00781810016107
Material	Aluminum Alloy
Plating Type	Unplated
UPC	781810016107
Die Index Run Side	426 - M
Die Index Tap Side	426 - M

Logistics

Minimum Pack Quantity	6
Carton Quantity	6
Pallet Quantity	216

Product Assets

[Catalog \[English\]](#)