



YPC40A36, Figure 6-shaped Connector

By Burndy

Catalog # [YPC40A36](#)

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:600 (61) - 800 (61)



Features

- Figure 6-Shaped Connector
- Separates Run and Tap Wires

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	600 kcmil-800 kcmil
Conductor - Copper Str Run	• 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil
Conductor - AL Str Run Range	600 kcmil-800 kcmil
Conductor - AL Str Run	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil
Conductor - AL Str Tap Range	397 kcmil-600 kcmil
Conductor - AL Str Tap	• 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor Type	• AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap

Conductor - ACSR Str Run Range	• ACSR C Str-Tap 556.5 kcmil-795 kcmil
Conductor - Copper Str Tap Range	397 kcmil-600 kcmil
Conductor - Copper Str Tap	• 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor - ACSR Str Tap Range	336.4 kcmil-556.5 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height inch	3.70 in
Package Weight	0.000 lb.
Dimension - Width inch	1.88 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	T
UPC	781810138700
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810138700
UPC 14 Digit GTIN	00781810138700

Logistics

Minimum Pack Quantity	1
Pallet Quantity	612
Carton Quantity	9

Product Assets

[Catalog \[English\]](#)



A Hubbell brand