

YPC40A40, Figure 6-shaped Connector

By Burndy
Catalog # [YPC40A40](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors.

Features

- Figure 6-Shaped Connector
- Separates Run and Tap Wires

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	600 kcmil-954 kcmil
Conductor - Copper Str Run	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil
Conductor - AL Str Run Range	600 kcmil-954 kcmil
Conductor - AL Str Run	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil
Conductor - AL Str Tap Range	600 kcmil-954 kcmil
Conductor - AL Str Tap	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil

Conductor Type	• 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap
Conductor - ACSR Str Run Range	556.5 kcmil-795 kcmil
Conductor - Copper Str Tap Range	600 kcmil-954 kcmil
Conductor - Copper Str Tap	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil
Conductor - ACSR Str Tap Range	556.5 kcmil-795 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height inch	3.74 in
Package Weight	0.000 lb.
Dimension - Width inch	1.88 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	97 mm
Dimension - Length Overall inch	3.84 in

General

Plated	N
--------	---

Trade Name	CRIMPIT™
Die Index	T
UPC	781810138755
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810138755
UPC 14 Digit GTIN	00781810138755

Logistics

Minimum Pack Quantity	1
Pallet Quantity	288
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand