



YRA1CU1, Aluminum Lug, Prefilled with Oxide Inhibitor

By Burndy
Catalog # YRA1CU1

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, Outside Dia: .56 IN

Features

- Aluminum Compression Lug
- Prefilled with PENETROX Oxide Inhibitor

Specifications

Buy American Compliant	Yes
Certification - cULus	No
Certification - UL Recognized	No
Buy America(n) Qualified	- Buy America Compliant (All status valid till December 2025) - Buy American Act Compliant (All status valid till December 2025) - BABA Compliant (All status valid till December 2025)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	1 AWG, 2 AWG, 3 AWG
Conductor - ACSR Str Size	2 AWG
Conductor - AL Str Size	1 AWG, 2 AWG
Conductor - AL Str Size Range	1 AWG - 2 AWG
Conductor - Copper Str Size Range	1 AWG - 3 AWG

Configuration

Physical Attribute - Pad Configuration	1 Hole
--	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in

Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.64 in
Dimension - L Length Overall mm	67 mm
Package Height	0.000 in
Dimension - Strip Length inch	1 in
Thickness - Pad	0.29 in
Dimension - B Length fraction	2-9/16 in
Dimension - B Length inch	0.960 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall inch	2.62 in
Dimension - D inch	1.19 in
Dimension - N inch	0.53 in

General

Die Index	243 - BG
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Physical Attribute - Tongue Type	Standard
Plated	N
UPC 12 Digit	781810016886
UPC 14 Digit GTIN	00781810016886
Material	Aluminum
Plating Type	Unplated
UPC	781810016886

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	19600

Product Assets

[Catalog \[English\]](#)