



YRA25U, Aluminum Lug, Prefilled with Oxide Inhitibor

By Burndy
Catalog # [YRA25U](#)



AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, Barrel Length: 1.43 IN

Features

- Aluminum Compression Lug
- Prefilled with PENETROX Oxide Inhibitor

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG

Configuration

Physical Attribute - Pad Configuration	1 Hole
--	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.91 in
Dimension - L Length Overall mm	81 mm
Package Height	0.000 in

Dimension - Strip Length inch	1.50 in
Thickness - Pad	0.25 in
Dimension - B Length fraction	3-1/4 in
Dimension - B Length inch	1.43 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall inch	3.19 in
Dimension - D inch	1.28 in
Dimension - N inch	0.62 in

General

Die Index	• 249 • K-840
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Physical Attribute - Tongue Type	Standard
Plated	N
UPC 12 Digit	781810810149
UPC 14 Digit GTIN	00781810810149
Material	Aluminum
Plating Type	Unplated
UPC	781810810149

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	14800

Product Assets

[Catalog \[English\]](#)