



YRA26U, Aluminum Lug, Prefilled with Oxide Inhibitor

By Burndy
Catalog # [YRA26U](#)

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX™, 3.19 IN L

Features

- Aluminum HYLUG for joining aluminum and copper cable to transformer and equipment pads
- Pre-filled with PENETROX Joint Compound and Capped

Application

For Joining Aluminum And Copper Cable To Transformer And Equipment Pads

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	2/0 AWG
Conductor - ACSR Str Size	2/0 AWG
Conductor - AL Str Size	2/0 AWG

Configuration

Physical Attribute - Pad Configuration	1 Hole
--	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter	0.91 in

Dimension - L Length Overall	81 mm
Dimension - Pad Width inch	0.91 in
Package Height	0.000 in
Dimension - Strip Length inch	1 1/2 in
Thickness - Pad	0.25 in
Dimension - B Length fraction	3-1/4 in
Dimension - B Length inch	1.43 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall	3.19 in
Dimension - D inch	1.28 in
Dimension - N inch	0.62 in

General

Die Index	• 249 • K-840
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Standard
Plated	N
Type	YRA
UPC 12 Digit	781810810163
UPC 14 Digit GTIN	00781810810163
Material	Aluminum
Plating Type	Unplated
UPC	781810810163

Logistics

Minimum Pack Quantity	50
Carton Quantity	50
Pallet Quantity	12000

Product Assets

[Catalog \[English\]](#)