

YRA28A, Aluminum Terminal

By Burndy
Catalog # [YRA28A](#)



Al Compression Terminal, 4/0 AWG ACSR/AI, 250 kcmil AI

Features

- Aluminum Compression Terminal

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	4/0 AWG
Conductor - AL Str Size	250 kcmil

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	1.43 in
Dimension - Outside Diameter inch	0.91 in
Dimension - L Length Overall mm	81 mm

Dimension - Pad Width inch	0.91 in
Package Height	0.000 in
Dimension - Strip Length inch	1 1/2 in
Thickness - Pad	0.25 in
Dimension - Length Overall inch	3.19 in
Dimension - D inch	1.28 in
Dimension - N inch	0.62 in

General

Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810089088
UPC 14 Digit GTIN	00781810089088
Material	Aluminum
Plating Type	Unplated
UPC	781810089088

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	14800

Product Assets

[Catalog \[English\]](#)