



YRA8CU1, Aluminum Lug, Prefilled with Oxide Inhibitor

By Burndy
Catalog # [YRA8CU1](#)



AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, 2.62 IN L, Pad Width: 15/16

Features

- Aluminum Compression Terminal
- Prefilled with PENETROX Oxide Inhibitor

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AL Str Size	8 AWG
Conductor - Copper Solid Size	8 AWG, 6 AWG
Conductor - Copper Solid Size Range	6 AWG- 8 AWG

Configuration

Physical Attribute - Pad Configuration	1 Hole
--	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.64 in
Dimension - L Length Overall mm	67 mm
Dimension - Pad Width inch	0.91 in

Package Height	0.000 in
Dimension - Strip Length inch	1 in
Thickness - Pad	0.29 in
Dimension - B Length fraction	2-9/16 in
Dimension - B Length inch	0.96 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall inch	2.62 in
Dimension - D inch	1.19 in
Dimension - N inch	0.53 in

General

Die Index	243 - BG
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Physical Attribute - Tongue Type	Standard
Plated	N
UPC 12 Digit	781810016862
UPC 14 Digit GTIN	00781810016862
Material	Aluminum
Plating Type	Unplated
UPC	781810016862

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	19600

Product Assets

[Catalog \[English\]](#)