



YRB2525TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB2525TW](#)

Cu Splice, 1/0(Cu)(Barrel A & B), 35 kV

Features

- Copper Compression Reducer
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1/0 AWG

Dimensions

Dimension - B Length inch	0.98 in
Dimension - Outside Diameter inch	0.51 in

Dimension - Length Overall inch	2.63 in
Dimension - Strip Length inch	1-1/16 in

General

Color Code	Pink
Trade Name	HYREDUCER™
Die Index	• 12 • 348
UPC	781810192825
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810192825
UPC 14 Digit GTIN	00781810192825

Logistics

Minimum Pack Quantity	1
Pallet Quantity	19200
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)