



YRB25U3TTN, Aluminum HYREDUCER Splice

By Burndy
Catalog # [YRB25U3TTN](#)

HYREDUCER



Features

- Aluminum Compression Reducer
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0 (19 STR) AWG
Conductor - Copper Str Size B	#3 (7 STR) AWG
Conductor - AL Str Size A	1/0 (19 STR) AWG
Conductor - AL Str Size B	#3 (7 STR) AWG

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - B Length inch	1.35 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Length Overall inch	3.25 in
Dimension - Strip Length inch	1-7/16 in

General

Color Code	- Orange - Tan
Trade Name	HYREDUCER™
Die Index	14 296
UPC	781810248522
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810248522
UPC 14 Digit GTIN	00781810248522

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)