



YRB2625TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB2625TW](#)

HYREDUCER

Features

- Copper Compression Reducer
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size B	1/0 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.04 in

Dimension - Outside Diameter	0.56 in
Dimension - Length Overall	2.36 in
Dimension - Strip Length inch	1-1/8 in

General

Color Code	Black
Trade Name	HYREDUCER™
Die Index	13
UPC	781810355299
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810355299
UPC 14 Digit GTIN	00781810355299

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)