



YRB2827TTN, Copper HYREDUCER Splice

By Burndy
Catalog # [YRB2827TTN](#)

HYREDUCER-TN CU

Features

- Copper Compression Reducer
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	3/0 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - B Length inch	1.16 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Length Overall inch	2.84 in

General

Color Code	Purple
Trade Name	HYREDUCER™
Die Index	15
UPC	781810439357
Material	Copper
UPC 12 Digit	781810439357
UPC 14 Digit GTIN	00781810439357

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)