



YRB2828TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB2828TW](#)

Copper Hyreducer; 2.84 in L; Hot Tin Dipped

Features

- Copper Compression Reducer
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG

Dimensions

Dimension - B Length inch	1.16 in
Dimension - Outside Diameter inch	0.69 in

Dimension - Length Overall inch	2.84 in
Dimension - Strip Length inch	1-7/32 in

General

Color Code	Purple
Trade Name	HYREDUCER™
Die Index	15
UPC	781810192849
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810192849
UPC 14 Digit GTIN	00781810192849

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)