



YRB282CTW, Copper - Compression Reducer



By Burndy
Catalog # [YRB282CTW](#)

4/0-2 CU HYREDUCER

Features

- Copper Compression Reducer
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	#2 AWG (STR)

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.16 in

Dimension - Outside Diameter	0.69 in
inch	
Dimension - Length Overall	2.84 in
inch	
Dimension - Strip Length inch	1-7/32 in

General

Color Code	Purple
Trade Name	HYREDUCER™
Die Index	15
UPC	781810297827
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810297827
UPC 14 Digit GTIN	00781810297827

Logistics

Minimum Pack Quantity	25
Pallet Quantity	9600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)