



YRB28U28TW, Aluminum - Compression Reducer

By Burndy
Catalog # [YRB28U28TW](#)

Aluminium Hyreducer Splice



Features

- Aluminum Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4/0 (19 STR) AWG
Conductor - Copper Str Size B	4/0 (19 STR) AWG
Conductor - AL Str Size A	4/0 (19 STR) AWG
Conductor - AL Str Size B	4/0 (19 STR) AWG

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.53 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Length Overall inch	3.69 in
Dimension - Strip Length inch	1-5/8 in

General

Color Code	White
Trade Name	HYREDUCER™
Die Index	298
UPC	781810192702
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810192702
UPC 14 Digit GTIN	00781810192702

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)