



# YRB2928TTN, Copper - Compression Reducer



By Burndy  
Catalog # [YRB2928TTN](#)

HYREDUCER™, Tin plated, 3.12 in long

## Features

- Copper Compression Reducer Splice
- Tin Plated

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | EX |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Conductor

|                               |           |
|-------------------------------|-----------|
| Conductor - Copper Str Size A | 250 kcmil |
| Conductor - Copper Str Size B | 4/O AWG   |

## Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - B Length inch         | 1.25 in |
| Dimension - Outside Diameter inch | 0.75 in |

|                                 |         |
|---------------------------------|---------|
| Dimension - Length BB inch      | 1.25 in |
| Dimension - Length Overall inch | 3.12 in |

## General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| Color Code        | Yellow         |
| Trade Name        | HYREDUCER™     |
| Die Index         | 16             |
| UPC               | 781810439432   |
| Material          | Copper         |
| Plating Type      | Tin Plated     |
| UPC 14 Digit GTIN | 00781810439432 |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 8700 |
| Carton Quantity       | 25   |

## Product Assets

[Catalog \[English\]](#)