



YRB2929TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB2929TW](#)

HYREDUCER™, Hot Tin dipped, 3.12 in long

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	250 kcmil
Conductor - Copper Str Size B	250 kcmil

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - B Length inch	1.25 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Length BB inch	1.25 in
Dimension - Length Overall inch	3.12 in

General

Color Code	Yellow
Trade Name	HYREDUCER™
Die Index	16
UPC	781810289358
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810289358

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)