



YRB2C2CT, Copper HYREDUCER Splice

By Burndy
Catalog # [YRB2C2CT](#)



HYREDUCER™, 2.21 in long

Features

- Copper Compression Reducer Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size B	2 AWG

Dimensions

Dimension - B Length inch	0.98 in
Dimension - Outside Diameter inch	0.42 in

Dimension - Length BB inch	0.98 in
Dimension - Length Overall inch	2.21 in

General

Color Code	Brown
Trade Name	HYREDUCER™
Die Index	10
UPC	781810367841
Material	Copper
UPC 14 Digit GTIN	00781810367841

Logistics

Minimum Pack Quantity	10
Pallet Quantity	48000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)