



YRB2C3CTTN, Copper HYREDUCER Splice, Tin Plated

By Burndy
Catalog # [YRB2C3CTTN](#)

HYREDUCER™, Tin plated, 2.21 in long



Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size B	3 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.98 in

Dimension - Outside Diameter	0.42 in
Dimension - Length BB inch	0.98 in
Dimension - Length Overall	2.21 in

General

Plated	Y
Color Code	Brown
Trade Name	HYREDUCER™
Die Index	10
UPC	781810439371
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810439371

Logistics

Minimum Pack Quantity	1
Pallet Quantity	48000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)