



YRB2U6TTN, Aluminum - Compression Reducer

By Burndy
Catalog # [YRB2U6TTN](#)

HYREDUCER™, Tin plated, 3.25 in long



Features

- Aluminum Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size B	6 AWG
Conductor - AL Str Size A	2 AWG
Conductor - AL Str Size B	6 AWG

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.35 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Length Overall inch	3.25 in
Dimension - Strip Length inch	1-7/16 in

General

Plated	Y
Trade Name	HYREDUCER™
Die Index	14 296
UPC	781810439395
Material	Aluminum
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810439395

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)