



YRB3028TTN, Copper - Compression Reducer



By Burndy
Catalog # [YRB3028TTN](#)

HYREDUCER™, Tin plated, 3.25 in long

Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	300 kcmil
Conductor - Copper Str Size B	4/0 AWG

Dimensions

Dimension - B Length inch	1.22 in
Dimension - Outside Diameter inch	0.81 in

Dimension - Length BB inch	1.22 in
Dimension - Length Overall inch	3.25 in
General	
Plated	Y
Color Code	White
Trade Name	HYREDUCER™
Die Index	• 17 • 298
UPC	781810439401
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810439401

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)