



YRB3125TTN, Copper HYREDUCER Splice, Tin Plated

By Burndy
Catalog # [YRB3125TTN](#)

HYREDUCER™, Tin plated, 3.34 in long



Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size B	1/0 AWG

Dimensions

Dimension - B Length inch	1.36 in
Dimension - Outside Diameter inch	0.88 in

Dimension - Length BB inch	1.36 in
Dimension - Length Overall inch	3.34 in
General	
Plated	Y
Color Code	Red
Trade Name	HYREDUCER™
Die Index	• 18 • 324
UPC	781810439418
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810439418

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4440
Carton Quantity	40

Product Assets

[Catalog \[English\]](#)