



YRB3129TW, Copper - Compression Reducer



By Burndy
Catalog # [YRB3129TW](#)

HYREDUCER™, Hot Tin dipped, 3.34 in long

Features

- Copper Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size B	250 kcmil

Dimensions

Dimension - B Length inch	1.36 in
Dimension - Outside Diameter inch	0.88 in

Dimension - Length BB inch	1.36 in
Dimension - Length Overall inch	3.34 in

General

Color Code	Red
Trade Name	HYREDUCER™
Die Index	• 18 • 324
UPC	781810297834
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810297834

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4640
Carton Quantity	40

Product Assets

[Catalog \[English\]](#)