



YRB31U25, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 1/0 AWG, AL9CU

By Burndy
Catalog # [YRB31U25](#)

Aluminum Tin Plated Splice Reducer, Barrel A 350 kcmil, Barrel B
1/0 AWG, AL9CU

Features

- Aluminum splice reducers are dual rated to accommodate both copper and aluminum wire
- Barrel features an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with crimp location bands
- Factory pre-filled with PENETROX™ Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel

Application

Wire Reducing Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size B	1/0
Conductor - Copper Str Run	350 KCMIL
Conductor - Material	ALUMINUM / COPPER
Conductor - AL Str Size A	350
Conductor - AL Str Size B	1/0
Conductor - AL Str Size A	350
Range	
Conductor - AL Str Run	350 KCMIL
Conductor - AL Str Size B	1/0
Range	
Conductor - AL Str Tap	1/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size	350



Conductor - Copper Str Size B	1/0
Range	
Conductor - Copper Str Tap	1/0 AWG

Configuration

Connector Type	DUAL RATED
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	15/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	65 mm
mm	
Dimension - B Length inch	0.95 in
Dimension - Outside Diameter	1.11 in
inch	
Dimension - Length Overall	2.54 in
inch	
Dimension - Strip Length inch	1/8

General

Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Trade Name	HYREDUCER™
Die Index	299
UPC	781810127889
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810127889
UPC 14 Digit GTIN	00781810127889

Logistics

Minimum Pack Quantity	25
Pallet Quantity	7400
Carton Quantity	25

Operational



A Hubbell brand