



YRB31U28TTN, Aluminum HYREDUCER Splice, Tin Plated

By Burndy
Catalog # [YRB31U28TTN](#)

HYREDUCER™, Tin plated 5.43 in long



Features

- Aluminum Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size B	4/O AWG
Conductor - AL Str Size A	350 kcmil
Conductor - AL Str Size B	4/O AWG

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Dimension - B Length inch	2.34 in
Dimension - Outside Diameter inch	1.11 in
Dimension - Length Overall inch	5.43 in
Dimension - Strip Length inch	2.5 in

General

Plated	Y
Color Code	Brown
Trade Name	HYREDUCER™
Die Index	299
UPC	781810439722
Material	Aluminum
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810439722

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2368
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)