



YRB31U28TW, Aluminum - Compression Reducer

By Burndy
Catalog # [YRB31U28TW](#)



HYREDUCER™, Hot Tin dipped, 5.43 in long

Features

- Aluminum Compression Reducer Splice
- Hot Tin Dipped

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size B	4/0 AWG
Conductor - AL Str Size A	350 kcmil
Conductor - AL Str Size B	4/0 AWG

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - B Length fraction	2-17/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.34 in
Dimension - Length Overall	5.43 in
inch	
Dimension - Strip Length inch	2.5 in

General

Color Code	Brown
Trade Name	HYREDUCER™
Die Index	299
UPC	781810192719
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 14 Digit GTIN	00781810192719

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2368
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)