



YRB3228TTN, Copper HYREDUCER Splice, Tin Plated



By Burndy
Catalog # [YRB3228TTN](#)

HYREDUCER™, Tin plated, 3.48 in long

Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size B	4/O AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.38 in

Dimension - Outside Diameter	0.95 in
Dimension - Length BB inch	1.38 in
Dimension - Length Overall	3.48 in

General

Plated	Y
Color Code	Blue
Trade Name	HYREDUCER™
Die Index	• 19 • 470
UPC	781810308288
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810308288

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)