



YRB322CTTN, Copper HYREDUCER Splice, Tin Plated



By Burndy
Catalog # [YRB322CTTN](#)

HYREDUCER™, Tin plated, 3.48 in long

Features

- Copper Compression Reducer Splice
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size B	2 AWG

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Outside Diameter inch	0.95 in

Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	3.48 in
General	
Plated	Y
Color Code	Blue
Trade Name	HYREDUCER™
Die Index	• 19 • 470
UPC	781810439463
Material	Copper
Plating Type	Tin Plated
UPC 14 Digit GTIN	00781810439463

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)